



## 2nd Floor wall mount pan

### design

Sieger Design

### codes

#220509 pan, P-trap  
suits concealed cistern  
#06899 seat, soft close with stainless  
steel hinges



### installation

Cistern We recommend using TECE in wall cisterns

### weight

total weight of pan and seat: 28.9 kg

### Australian Standards & WELS

#220509 AS 1172.2:1999  
WELS 3 Star

### instructions

Wall mount pans require support within the wall to ensure correct function and safety.

1. When installing wall hung toilets we recommend using TECE in wall cisterns although most other manufacturers will be suitable. Please read manufactures installation instructions prior to installing.
2. When using a concealed cistern and frame as 1 unit please ensure the cistern fastenings are secured into masonry structures. When installed into stud frame work following manufacturer's instructions.
3. For stability there should be no movement in the cistern frame work, any movement will cause the finished surface to crack
4. There cannot be any gaps between the concealed cistern, the sheeting (compressed wall or floor sheeting 8-10mm thick) and the finished surface (tiles or stone etc). Any gaps will cause movement and cracks.

